



Inlet Seals for Agilent 7890/6890/6850 GC Systems



Ohio Valley is now offering Gold-Plated and Stainless Steel Inlet Seals for the Agilent 7890/6890/68500 GC Systems.

Two different types are available — Splitless Single Groove and Split Double Groove (Cross). All seals are supplied with washers.

The Double Groove (Cross) Inlet Seal is ideal for high-flow split applications.

Inlet seals should be changed often because they come in contact with the sample. You will want to prevent absorption of active compounds and the buildup of sample residue and septum fragments on the disc surface.

By using inlet seals, oxygen is unable to pass into the carrier gas, which will increase the capillary column lifetime. Inlet seals also reduce detector noise of high-sensitivity detectors.

We recommend using the gold-plated inlet seal to reduce the absorption of active compounds. Also, the gold-plated inlet seal is ideal for Mass Spec, trace level analyses and for use in toxicology and drugs of abuse labs.

A complete list of part numbers is listed on the next page.



Available from:

PhaseSep Pty Ltd - PO Box 3346, Doncaster East, VIC, 3109
admin@phsep.com www.phsep.com



OV Part Number	Description	Unit
4300	0.8mm Inlet Seal, Gold-plated For Agilent Systems, Splitless, with Gold-plated Washers	2/pk
4300-10	0.8mm Inlet Seal, Gold-plated For Agilent Systems, Splitless, with Gold-plated Washers	10/pk
4350	0.8mm Inlet Seal, Stainless Steel For Agilent Systems, Splitless, with SS Washers	2/pk
4350-10	0.8mm Inlet Seal, Stainless Steel For Agilent Systems, Splitless, with SS Washers	10/pk
4400	0.8mm Inlet Seal, Gold-plated For Agilent Systems, Split Double Groove (Cross), with Gold-plated Washers	2/pk
4400-10	0.8mm Inlet Seal, Gold-plated For Agilent Systems, Split Double Groove (Cross), with Gold-plated Washers	10/pk
4450	0.8mm Inlet Seal, Stainless Steel For Agilent Systems, Split Double Groove (Cross), with SS Washers	2/pk
4450-10	0.8mm Inlet Seal, Stainless Steel For Agilent Systems, Split Double Groove (Cross), with SS Washers	10/pk
4800	Replacement Gold-plated Washers for Inlet Seal	12/pk
4850	Replacement Stainless Steel Washers for Inlet Seal	12/pk



Available from:

PhaseSep Pty Ltd - PO Box 3346, Doncaster East, VIC, 3109
 admin@phsep.com www.phsep.com

